

GUCCI

METHOD 1: HOW TO MEASURE YOUR CURRENT RING

CONFIRM PRINTED PAPER SIZE

Bar A (mm)



Bar B (inch)



Ring measurements are very precise. Carefully follow these instructions to obtain an accurate measurement.


1. Prior to printing, ensure that Page Scaling is set to "None" on your print dialog box. (To open the print dialog box, press CTRL+P.)

2. Measure the bar on the left (Bar A or Bar B). It must be exactly 2 inches or 50 mm long.


MEASURE CURRENT RING

Steps:


1. Select a ring that properly fits the intended finger.
2. Place the ring over the circles below. Match the inside edge of the ring to the circle nearest in size. This measurement refers to the inside diameter of the ring.
3. If the ring falls between two sizes, order the larger size.



The sizes of the rings below are in Italian.



MEASUREMENTS MATCH THE
INSIDE EDGE OF THE RING



GUCCI

METHOD 2: HOW TO MEASURE YOUR FINGER

CONFIRM PRINTED PAPER SIZE

Bar A (mm)



Bar B (inch)



Ring measurements are very precise. Carefully follow these instructions to obtain an accurate measurement.



1. Prior to printing, ensure that Page Scaling is set to "None" on your print dialog box. (To open the print dialog box, press CTRL+P.)

2. Measure the bar on the left (Bar A or Bar B). It must be exactly 2 inches or 50 mm long.

MEASURE FINGER WITH PAPER SIZER

Steps:

1. carefully cut along the outline of the sizer. make a small slit in the left end of the sizer
2. wrap the sizer around the intended finger with the numbers facing out.
3. slide the pointed end of the sizer through the slit.
4. move the sizer to the larger part of the finger, this may be the knuckle.
5. pull tightly. the sizer must fit snugly to produce an accurate size.
6. the number that lines up at the slit represents the ring size for that finger.



Italy Gucci size	Circumference (mm)
1	40,8
2	41,8
3	42,7
4	44
5	44,9
6	45,8
7	46,8
8	48
9	49
10	50,2
11	50,9
12	51,8
13	52,8
14	54

Italy Gucci size	Circumference (mm)
15	54,6
16	55,9
17	56,8
18	58,1
19	59
20	60,3
21	61,2
22	62,2
23	62,8
24	64,1
25	64,7
26	65,9
27	66,6